

HPP271 Hydrogen Peroxide Probe

		1 2 3 4 5						
Vaisala PEROXCAP Hydrogen Peroxide Probe		HPP271					0	PRICE
Probe options	4..20 mA output signals	OFF (typical for ch2)		N	N			
	scaling for ch1 and ch2	H2O2 0...2000 ppm (typical for ch1)		A	A			
	Note! Includes Modbus RTU over RS-485	Channel 1						
		Channel 2						
	Special features	None					0	
Other options	Cable	no cable					N	
		<i>Probe cable with open wires (1.5 m)</i>					A	
		<i>Probe cable with open wires (3 m)</i>					B	
		<i>Probe cable with open wires (5 m)</i>					C	
		<i>Probe cable with open wires (10 m)</i>					D	
	Additional options	None					0	

Selections in bold are included in the prices of the basic version.
Selections in italic are available at an extra price.

Examples of order codes with typical settings:

Standard vaporized hydrogen peroxide probe for demanding decontamination application **HPP271** **A** **N** **0** **B** **0**

1 2 3 4 5

End customer: _____

Accessories

USB cable for PC connection	242659
Filter Cap Porous PTFE	DRW246363SP
Probe cable with open wires (1.5 m)	254294SP
Probe cable with open wires (3 m)	254295SP
Probe cable with open wires (5 m)	254296SP
Probe cable with open wires (10 m)	254297SP
Probe cable with open wires and 90° plug (0.6 m)	244669SP
Gland set for through-wall installation, HPP271	HPP271MOUNTINGSET1
Flange for Through-wall Installation, HPP271	HPP271MOUNTINGSET2
Wall Mount for HPP271 and HPP272	HPP272WALLMOUNT
Cable between HPP270 and Indigo 201 (1.5 m)	INDIGOCABLEHD1M5
Cable between HPP270 and Indigo 201 (3 m)	INDIGOCABLEHD3M
Cable between HPP270 and Indigo 201 (5 m)	INDIGOCABLEHD5M
Cable between HPP270 and Indigo 201 (10 m)	INDIGOCABLEHD10M

HPP272 Hydrogen Peroxide, Humidity and Temperature Probe

				1	2	3	4	5	6	
Vaisala PEROXCAP Hydrogen Peroxide and Humidity and Temperature Probe		HPP272						0	N	PRICE
Probe options and set	4..20 mA output signals	H2O2 0...2000 ppm (typical for ch1)		A	A					
	scaling for ch1 and ch2	RS (H2O2 and H2O) 0...100% (typical for ch2)		B	B					
	Note! Includes Modbus RTU over RS-485	Temperature Range +5...+70C		C	C					
		RH (H2O only) 0...100%		D	D					
		H2O 0... 445 870 ppm		E	E					
	Channel 1									
	Channel 2									
	Special features	None						0		
Other options	Cable	no cable							N	
		<i>Probe cable with open wires (1.5 m)</i>							A	
		<i>Probe cable with open wires (3 m)</i>							B	
		<i>Probe cable with open wires (5 m)</i>							C	
		<i>Probe cable with open wires (10 m)</i>							D	
	Additional options	None						0		
	For Future use	None							N	

Selections in bold are included in the prices of the basic version.
Selections in italic are available at an extra price.

Examples of order codes with typical settings:

HPP272	A	B	0	N	0	N
	1	2	3	4	5	6

End customer: _____

Accessories

USB cable for PC connection
Filter Cap Porous PTFE
Probe cable with open wires (1.5 m)
Probe cable with open wires (3 m)
Probe cable with open wires (5 m)
Probe cable with open wires (10 m)
Probe cable with open wires and 90° plug (0.6 m)
Gland set for through-wall installation, HPP272

Item code

242659
DRW246363SP
254294SP
254295SP
254296SP
254297SP
244669SP
HPP272MOUNTINGSET1